## बीरबल साहनी पुराविज्ञान संस्थान, लखनऊ BIRBAL SAHNI INSTITUTE OF PALAEOSCIENCES, LUCKNOW

टेलीग्राम पेलियोबॉटनी दूरभाष 2740008,2742983 फैक्स ९१-91-522-2740485, 2740098 बी सा पु सं /III/भंडार एवं क्रय/R.A. 53, विश्व विद्यालय मार्ग लखनऊ - 226007

Date: 08.01.2019

संयोजक वेबसाइट समिति, बी सा पु सं, लखनऊ।

## Heating Digital Shaking Drybath (Specifications at the back)

Subject: -----

Dear Sirs,

This Institute intend to purchase item mentioned above. Sealed quotations are invited so as to reach this office on or before 5:00 P.M. on 24.01.2019 duly superscribed by "Heating Digital Shaking Drybath"

While submitting quotation please note that:

- The material may either of indigenous manufacturer or of foreign make, available from ready stock. Any offer to supply on forward Delivery Basis under suppliers own quota license will also be considered.
- 2. The price quoted should be F.O.R. Destination.
- 3. Your rates should include packing, insurance and forwarding charges.
- 4. The rates of GST should be clearly indicated wherever chargeable. The tendered should also indicate GST Registration Number and date in this quotation.
- 5. Specific mention should be made whether the offer is for supplies available exstock. In case the officer is on Forward Delivery basis, firm delivery period must be indicated.
- The cover should be sealed and superscribed "Quotation for "Heating Digital Shaking Drybath" must be written on envelope. The quotations not complying the procedure will be rejected.
- 7. Payments will be made by crossed cheque on The Indian Overseas Bank, Lucknow only after receipt and acceptance of supply and installation/ if required satisfactory.
- The acceptance of the quotation will rest with the Director who does not bind himself to accept the lowest quotation and reserves the right to himself to reject or partially accept any or all the quotation received without assigning any reasons.
- The quotations are liable to be cancelled if any of the above mentioned conditions are not complied with.
- 10. The items may be increase or decrease at the time of purchase.

(Swapna Mazumdar)
Section Officer
Store & Purchase Section

S.N.	Item Description & Specification	Qty.
1.	Heating Digital Shaking Drybath, Speed Range from 150 to 1500 RPM block dependent, Temperature range 5°C to 100°C, Temperature accuracy 0.5°C to 80°C	01
2.	0.5ml Tube Block Set with Cover, SHAKE/HEAT BLOCK 0.5 WELL Max. Mountable Tubes-48	01
3.	1.5ml Tube Block Set with Cover, SHAKE/HEAT BLOCK 1.5 ML, Max. Mountable Tubes-24	01
4.	50ml Tube Block Set with Cover, SHAKE/HEAT BLOCK 50 ML, Max. Mountable Tubes-06	01