

बीरबल साहनी पुराविज्ञान संस्थान, लखनऊ
BIRBAL SAHNI INSTITUTE OF PALAEOSCIENCES, LUCKNOW

टेलीग्राम पेलियोबॉटनी

दूरभाष 2740008,2742983

फैक्स ९१-91-522-2740485,2740098

बी सा पु सं /III/भंडार एवं क्रय/C-728

संयोजक वेबसाइट समिति,

बी सा पु सं, लखनऊ

53, विश्व विद्यालय मार्ग

लखनऊ - 226007

Date: 05.09.2017

Upright Freezer, -86°C, Ultra Low Temperature, with Urethane Insulation, 230V, 50 Hz
(specification at the back)

Subject: -----

Dear Sirs,

This Institute intend to purchase item mentioned above. Sealed quotations are invited so as to reach this office on or before 5:00 P.M. on 29.09.2017 duly superscribed by "Upright Freezer, -86°C, Ultra Low Temperature, with Urethane Insulation, 230V, 50 Hz".

While submitting quotation please note that:

1. The material may either of indigenous manufacturer or of foreign make, available from ready stock. Any offer to supply on forward Delivery Basis under suppliers own quota license will also be considered.
2. The price quoted should be F.O.R. Destination.
3. Your rates should include packing, insurance and forwarding charges.
4. The rates of Sales Tax should be clearly indicated wherever chargeable. The tendered should also indicate Central/Sales Tax Registration Number and date in this quotation.
5. Specific mention should be made whether the offer is for supplies available ex-stock. In case the officer is on Forward Delivery basis, firm delivery period must be indicated.
6. The cover should be sealed and superscribed "Quotation for "Upright Freezer, -86°C, Ultra Low Temperature, with Urethane Insulation, 230V, 50 Hz" must be written on envelope. The quotations not complying the procedure will be rejected.
7. Payments will be made by crossed cheque on The Indian Overseas Bank, Lucknow only after receipt and acceptance of supply and installation/ if required satisfactory.
8. The acceptance of the quotation will rest with the Director who does not bind himself to accept the lowest quotation and reserves the right to himself to reject or partially accept any or all the quotation received without assigning any reasons.
9. The quotations are liable to be cancelled if any of the above mentioned conditions are not complied with.
10. The quantity may be increase or decrease at the time of purchase.


(Sanjay Kumar)
Registrar

DESCRIPTION	QTY
<p>Upright Freezer, -86°C Ultra-Low Temperature, with Urethane Foam Insulation, 230V, 50Hz</p> <p>Technical Specification:</p> <p>Capacity: 410 L; 14.5 Cu. Ft.</p> <p>Temp Range: -Programmable temperature range from -50°C to -86°C in 1°C increments, even at ambient temperature upto 32°C</p> <p>Control: Micro Processor control of temperature and alarms with non-volatile memory</p> <p>Circulation: Requires just one fan for reduced power consumption and noise.</p> <p>Cascade Refrigeration: Hermetically-sealed twostage cascade system with capacity to cope in high-ambient conditions</p> <p>Insulation: Polyurethane foam, 5.1", 130 mm thick Chamber: Latch able inner door to minimize cold air loss when external door is opened and reduce power consumption to maintain temperature.</p> <p>Shelves : 5 compartment with 4 adjustable height corrosion resistant Stainless Steel Shelves. Each compartment is well equipped with Insulated Inner Door with magnetic lock</p> <p>System Monitoring & Reporting Technology Software built-In for Fault diagnosis or set point variance</p> <p>Security: Keyed locks on the outer doors and lids keep out unauthorized users</p> <p>Password: 4-digit password prevents unauthorized users from changing the temperature setpoint or alarm setpoint.</p> <p>Power: On-Off switch is located behind the locked panel, preventing power from being accidentally turned off.</p> <p>Battery Backup: Activates alarms and display temperature during power outage.</p> <p>"Alarms: Audible and Visible alarms for Temperature filter clean, power out, Low Battery, System Fail, and Fault analysis.</p> <p><i>Nureg Rev</i></p>	1